

# Eaton XTSCP16BBMA

Catalog Number: XTSCP16BBMA

Eaton XT IEC FVR Manual Motor Controller, 0.16A, 45 mm Frame size, 24V 50 Hz coil

## General specifications



Photo is representative

### Product Name

Eaton XT IEC motor control

### UPC

786680187292

### Product Height

7.03 in

### Product Weight

4 lb

### Catalog Number

XTSCP16BBMA

### Product Length/Depth

1.77 in

### Product Width

3.77 in

### Certifications

UL Listed file E245398

IEC 60947

UL 508

### Catalog Notes

For 200 and 240V horsepower rating calculate motor rating according to rated current. Specified values to NEC 430.6(A)(1).

**Amperage Rating**

0.16A

**HP rating - max**

1/2 Hp at 480 and 600V

**Type**

Factory-assembled

**Frame size**

45 mm, 0.1 to 32 A

**Auxiliary contacts**

1 NO, 1 NC

**Coil voltage**

110-120 Vac, 50/60 Hz

**Frame**

B

**Full load current range**

0.1-0.16 A

**Special features**

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 3.2A

**Phase**

Three-phase

**Class**

Class 10

**Catalogs**[Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTSCP16BBMA](#)