

Eaton XTSCP25BBMT

Catalog Number: XTSCP25BBMT

Eaton XT IEC FVR Manual Motor Controller, 6.3A, 45 mm Frame size, 42V 50 Hz, 48V 60 Hz coil,

General specifications



Photo is representative

Product Name

Eaton XT IEC motor control

UPC

786680187209

Product Height

7.03 in

Product Weight

4 lb

Catalog Number

XTSCP25BBMT

Product Length/Depth

1.77 in

Product Width

3.77 in

Certifications

UL 508

IEC 60947

UL Listed file E245398

CSA file No. 229767, Class 3211-05

Catalog Notes

For 200 and 240V horsepower rating calculate motor rating according to rated current. Specified values to NEC 430.6(A)(1).

Amperage Rating

0.25A

HP rating - max

1/2 Hp at 480 and 600V

Type

Factory-assembled

Frame size

45 mm, 0.1 to 32 A

Auxiliary contacts

1 NO, 1 NC

Coil voltage

24 Vac, 50/60 Hz

Frame

B

Full load current range

0.16-0.25 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 3.5A

Phase

Three-phase

Class

Class 10

Catalogs[Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTSCP25BBMT](#)