

Eaton XTSCP63BBMD

Catalog Number: XTSCP63BBMD

Eaton XT IEC FVR Manual Motor Controller, 1.6A, 45 mm Frame size, 12 Vdc coil,

General specifications



Photo is representative

Product Name

Eaton XT IEC motor control

UPC

786680186134

Product Height

7.03 in

Product Weight

4 lb

Catalog Number

XTSCP63BBMD

Product Length/Depth

1.77 in

Product Width

3.77 in

Certifications

IEC 60947

UL 508

UL Listed file E245398

CSA file No. 229767, Class 3211-05

Catalog Notes

For 200 and 240V horsepower rating calculate motor rating according to rated current. Specified values to NEC 430.6(A)(1).

Amperage Rating

0.63A

HP rating - max

1/2 Hp at 480 and 600V

Type

Factory-assembled

Frame size

45 mm, 0.1 to 32 A

Auxiliary contacts

1 NO, 1 NC

Coil voltage

600 Vac, 60 Hz

Frame

B

Full load current range

0.4-0.63 A

Special features

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 8.82A

Phase

Three-phase

Class

Class 10

Catalogs[Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTSCP63BBMD](#)