

# Eaton XTSCP63BBMN

Catalog Number: XTSCP63BBMN

Eaton XT IEC FVR Manual Motor Controller, 2.5A, 220 Vdc coil, 45 mm Frame size

## General specifications



Photo is representative

### Product Name

Eaton XT IEC motor control

### UPC

786680186226

### Product Height

7.03 in

### Product Weight

4 lb

### Catalog Number

XTSCP63BBMN

### Product Length/Depth

1.77 in

### Product Width

3.77 in

### Certifications

IEC 60947

UL 508

UL Listed file E245398

CSA file No. 229767, Class 3211-05

### Catalog Notes

For 200 and 240V horsepower rating calculate motor rating according to rated current. Specified values to NEC 430.6(A)(1).

**Amperage Rating**

0.63A

**HP rating - max**

1/2 Hp at 480 and 600V

**Type**

Factory-assembled

**Frame size**

45 mm, 0.1 to 32 A

**Auxiliary contacts**

1 NO, 1 NC

**Coil voltage**

400 Vac, 50 Hz

**Frame**

B

**Full load current range**

0.4-0.63 A

**Special features**

Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 8.82A

**Phase**

Three-phase

**Class**

Class 10

**Catalogs**[Motor Control and Protection](#)**Specifications and datasheets**[Eaton Specification Sheet - XTSCP63BBMN](#)