

# Eaton Y25G28T09A

Catalog Number: Y25G28T09A

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 103, 60 Hz, three-phase, 220 V, 208Y/120 V, 2 at -5% FCBN, 115 °C rise, 9 KVA, indoor-outdoor, 70Q

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	Y25G28T09A
	<b>UPC</b>
	786680009846
<b>Product Length/Depth</b>	<b>Product Height</b>
10.01 in	15.9 in
<b>Product Width</b>	<b>Product Weight</b>
16.93 in	198 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	<b>Catalog Notes</b>
	Model A

## Physical Attributes

### Coil material

Aluminum

### Design

EPT

### Enclosure

NEMA 3R

### Frame

103

### Tap size

2 at -5% FCBN

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

70Q

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Three-phase

### Primary voltage

220 V

### Secondary Voltage

208Y/120 V

### Temperature rise

115 °C rise

### Volt ampere rating

9 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Y25G28T09A](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)