

Eaton Y25G43T09

Catalog Number: Y25G43T09

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 103, 60 Hz, three-phase, 220 V, 416 V, 2 at -5% FCBN, 115 °C rise, 9 KVA, indoor-outdoor, 560E

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y25G43T09
	UPC
	786680095863

Product Length/Depth	Product Height
10.01 in	15.9 in

Product Width	Product Weight
16.93 in	184 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

103

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

560E

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

220 V

Secondary Voltage

416 V

Temperature rise

115 °C rise

Volt ampere rating

9 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y25G43T09

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)