

Eaton Y29D28E15B

Catalog Number: Y29D28E15B

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 95, 60 Hz, three-phase, 208 V, 208Y/120 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 86A

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y29D28E15B
	UPC
	786680320071

Product Length/Depth	Product Height
10.52 in	17.38 in

Product Width	Product Weight
20 in	250 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

95

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

86A

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

208 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y29D28E15B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)