

# Eaton Y29M12T30SS

Catalog Number: Y29M12T30SS

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 243, 60 Hz, three-phase, 208 V, 120 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor, 85J



Photo is representative

## General specifications

<a href="#">Product Name</a>	<a href="#">Catalog Number</a>
Eaton General purpose encapsulated transformer	Y29M12T30SS
	<a href="#">UPC</a>
	786680108709

<a href="#">Product Length/Depth</a>	<a href="#">Product Height</a>
10.52 in	17.38 in

<a href="#">Product Width</a>	<a href="#">Product Weight</a>
20 in	511 lb

<a href="#">Warranty</a>	<a href="#">Certifications</a>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified
	<a href="#">Catalog Notes</a>
	Grade 304 Stainless Steel Enclosure

## Physical Attributes

### Coil material

Aluminum

### Design

EPT

### Enclosure

NEMA 3R

### Frame

243

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

General-purpose encapsulated transformer

### Wiring connection

85J

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Three-phase

### Primary voltage

208 V

### Secondary Voltage

120 V

### Temperature rise

115 °C rise

### Volt ampere rating

30 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Y29M12T30SS](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)