

Eaton Y29M29T45CUS6

Catalog Number: Y29M29T45CUS6

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 244, 60 Hz, three-phase, 208 V, 208 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 45 KVA, indoor-outdoor, 85M



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y29M29T45CUS6
	UPC
	786680095917
Product Length/Depth	Product Height
14.66 in	28.15 in
Product Width	Product Weight
26.58 in	802 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Grade 316 stainless steel enclosure

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

244

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

85M

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

208 V

Secondary Voltage

208 V

Temperature rise

115 °C rise

Volt ampere rating

45 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y29M29T45CUS6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)