

# Eaton Y29M48T30CU

Catalog Number: Y29M48T30CU

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 243, 60 Hz, three-phase, 208 V, 480 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor, 57B



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	Y29M48T30CU
	<b>UPC</b>
	786680108686
<b>Product Length/Depth</b>	<b>Product Height</b>
10.52 in	17.38 in
<b>Product Width</b>	<b>Product Weight</b>
20 in	617 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

## Physical Attributes

### Coil material

Copper

### Design

EPT

### Enclosure

NEMA 3R

### Frame

243

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

General-purpose encapsulated transformer

### Wiring connection

57B

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Three-phase

### Primary voltage

208 V

### Secondary Voltage

480 V

### Temperature rise

115 °C rise

### Volt ampere rating

30 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Y29M48T30CU](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)