

Eaton Y38D37T15CUSS

Catalog Number: Y38D37T15CUSS

Eaton, general purpose encapsulated transformer, ept, three-phase, pv: 380v, taps: 2 at +2.5% fcan, 2 at -2.5% fcbn, sv: 380y/220v, 115°C, 15 kva, cu windings, frame: 95, indoor-outdoor.

General specifications



Photo is representative

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

Y38D37T15CUSS

UPC

786680099434

Product Length/Depth

10.52 in

Product Height

17.38 in

Product Width

20 in

Product Weight

247 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Grade 304 stainless steel enclosure

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

95

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

72E

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

380 V

Secondary Voltage

380Y/220 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y38D37T15CUSS](#)