

Eaton Y38G25T15X

Catalog Number: Y38G25T15X

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 96, 50-60 Hz, three-phase, 380 V, 220 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 543E

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y38G25T15X
	UPC
	786680056406

Product Length/Depth	Product Height
9.42 in	16.19 in

Product Width	Product Weight
29.68 in	330 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

96

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

543E

Performance Ratings

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

380 V

Secondary Voltage

220 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y38G25T15X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)