

Eaton Y38G31T15X

Catalog Number: Y38G31T15X

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 95, 50-60 Hz, three-phase, 380 V, 220Y/127 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 70F

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y38G31T15X
	UPC
	786680012105
Product Length/Depth	Product Height
10.52 in	17.38 in
Product Width	Product Weight
20 in	260 lb

Warranty **Certifications**

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

95

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

70F

Performance Ratings

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

380 V

Secondary Voltage

220Y/127 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y38G31T15X](#)