

Eaton Y38M37T30X

Catalog Number: Y38M37T30X

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 244, 50-60 Hz, three-phase, 380 V, 380Y/220 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor, 84H



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y38M37T30X
	UPC
	786680012266
Product Length/Depth	Product Height
14.66 in	28.15 in
Product Width	Product Weight
26.58 in	697 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

244

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

84H

Performance Ratings

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

380 V

Secondary Voltage

380Y/220 V

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y38M37T30X



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia