

Eaton Y39G28T06CU

Catalog Number: Y39G28T06CU

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 200, 60 Hz, three-phase, 400 V, 208Y/120 V, 2 at -5% FCBN, 115 °C rise, 6 KVA, indoor-outdoor, 70T

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y39G28T06CU
	UPC
	786680108426

Product Length/Depth	Product Height
10.01 in	15.9 in

Product Width	Product Weight
16.93 in	184 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

200

Tap size

2 at -5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

70T

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

400 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Volt ampere rating

6 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y39G28T06CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)