

# Eaton Y39G34T15X

Catalog Number: Y39G34T15X

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 96, 50-60 Hz, three-phase, 400 V, 400Y/231 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 66E

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	Y39G34T15X
	UPC
	786680012709

<b>Product Length/Depth</b>	<b>Product Height</b>
9.42 in	16.19 in

<b>Product Width</b>	<b>Product Weight</b>
29.68 in	321 lb

<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

EPT

### Enclosure

NEMA 3R

### Frame

96

### Tap size

2 at -5% FCBN

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

66E

## Performance Ratings

### Frequency rating

50-60 Hz

### Phase

Three-phase

### Primary voltage

400 V

### Secondary Voltage

400Y/231 V

### Temperature rise

115 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Y39G34T15X](#)