

Eaton Y42D28T06N

Catalog Number: Y42D28T06N

General-Purpose Encapsulated Transformer, EPT, Three-phase, PV: 2400V, Taps: 2 at +2.5% FCAN, 2 at -2.5% FCBN, SV: 208/120V, 115°C, 6 kVA, Al windings, Frame: 97, Indoor-Outdoor

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer medium voltage	Y42D28T06N
	UPC
	786680327445
Product Length/Depth	Product Height
8.38 in	11.06 in
Product Width	Product Weight
25.68 in	200 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Not Applicable from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	Model N

defaultTaxonomyAttributeLabel

Type

General-Purpose Encapsulated Transformer

Coil material

Aluminum

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

2,400 V

Secondary Voltage

208/120 V

Temperature rise

115 °C rise

Design

EPT

Enclosure

NEMA 3R

Frame

97

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Volt ampere rating

6 kVA

Weathershield

Indoor-Outdoor

Wiring connection

65B

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - Y42D28T06N](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)