

Eaton Y43M24T30X

Catalog Number: Y43M24T30X

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 243, 50-60 Hz, three-phase, 416 V, 240 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y43M24T30X
	UPC
	786680013256
Product Length/Depth	Product Height
10.52 in	17.38 in
Product Width	Product Weight
20 in	422 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

243

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Performance Ratings

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

416 V

Secondary Voltage

240 V

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y43M24T30X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)