

Eaton Y44M25T30CU

Catalog Number: Y44M25T30CU

Eaton General purpose encapsulated transformer, EPT, copper, 243, 60 Hz, three-phase, 440 V, 220 V, 2 at +2.5% FCAN 4 at -2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor, 85l



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y44M25T30CU
	UPC 786680115622
Product Length/Depth	Product Height
10.52 in	17.38 in
Product Width	Product Weight
20 in	0.001 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified

Physical Attributes

Coil material

Copper

Design

EPT

Frame

243

Tap size

2 at +2.5% FCAN 4 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

85I

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

440 V

Secondary Voltage

220 V

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y44M25T30CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)