

Eaton Y48D28T15CULS45

Catalog Number: Y48D28T15CULS45

Eaton General purpose encapsulated transformer, dry type distribution transformer, copper, 95, 60 Hz, low sound 45 dB, three-phase, 480 V, 208Y/120 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 115 °C rise, 15 KVA, 72B

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48D28T15CULS45
	UPC
	786680060953
Product Length/Depth	Product Height
10.52 in	17.38 in
Product Width	Product Weight
20 in	295 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Low sound equal to 45 dB

Physical Attributes

Coil material

Copper

Frame

95

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Wiring connection

72B

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Modification 1

Low sound 45 dB

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y48D28T15CULS45](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)