

Eaton Y48D28T15CUS64X

Catalog Number: Y48D28T15CUS64X

Eaton, general purpose encapsulated transformer, ept three-phase 480v 2 at +2.5% fcan 2 at -2.5% fcbn 208y/120v 115°c 15 kva copper windings 954x 72b indoor-outdoor 60 hz nema 4x



Photo is representative

General specifications

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

Y48D28T15CUS64X

UPC

786680100284

Product Length/Depth

10.52 in

Product Height

17.38 in

Product Width

20 in

Product Weight

0.001 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CSA Certified

Catalog Notes

NEMA 4X Grade 316 stainless steel enclosure.



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 4X

Frame

954X

Tap size

2 at +2.5% FCAN 2 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y48D28T15CUS64X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)