

Eaton Y48D28T15CUS6LS45

Catalog Number: Y48D28T15CUS6LS45

Eaton General purpose encapsulated transformer, EPT, copper, 95, 60 Hz, three-phase, 480 V, 208Y/120 V, 2 at +2.5% FCAN 2 at -2.5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 72B



Photo is representative

General specifications

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

Y48D28T15CUS6LS45

UPC

786680115608

Product Length/Depth

10.52 in

Product Height

17.38 in

Product Width

20 in

Product Weight

0.001 lb

Warranty

Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Grade 316 stainless steel enclosure (does not imply NEMA 4X rating) Low sound design equivalent to 45 dB.

Physical Attributes

Coil material

Copper

Design

EPT

Frame

95

Tap size

2 at +2.5% FCAN 2 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

72B

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y48D28T15CUS6LS45](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)