

Eaton Y48D47T15CUSS

Catalog Number: Y48D47T15CUSS

Eaton General purpose encapsulated transformer, EPT, copper, 95, 60 Hz, three-phase, 480 V, 480Y/277 V, 2 at +2.5% FCAN 2 at -2.5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 72C



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48D47T15CUSS
	UPC
	786680115585
Product Length/Depth	Product Height
10.52 in	17.38 in
Product Width	Product Weight
20 in	295 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	Catalog Notes
	Grade 304 stainless steel enclosure (does not imply a NEMA 4X rating).

Physical Attributes

Coil material

Copper

Design

EPT

Frame

95

Tap size

2 at +2.5% FCAN 2 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

72C

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y48D47T15CUSS](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)