

Eaton Y48G24T03CUSS

Catalog Number: Y48G24T03CUSS

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 201, 60 Hz, three-phase, 480 V, 240 V, 2 at -5% FCBN, 115 °C rise, 3 KVA, indoor-outdoor, 74A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48G24T03CUSS
	UPC
	786685355115
Product Length/Depth	Product Height
8.26 in	13.4 in
Product Width	Product Weight
15.93 in	62 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Grade 304 stainless steel enclosure

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

201

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

74A

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

240 V

Temperature rise

115 °C rise

Volt ampere rating

3 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y48G24T03CUSS

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)