

Eaton Y48G28B09LS42

Catalog Number: Y48G28B09LS42

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 95, 60 Hz, low sound 42 dB, three-phase, 480 V, 208Y/120 V, 2 at -5% FCBN, 80 °C rise, 9 KVA, indoor-outdoor, 70A

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48G28B09LS42
	UPC
	786680052965

Product Length/Depth	Product Height
10.52 in	17.38 in

Product Width	Product Weight
20 in	475 lb

Warranty	Certifications
-----------------	-----------------------

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Low sound equal to 42 dB

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

95

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

70A

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

80 °C rise

Volt ampere rating

9 kVA

Miscellaneous

Modification 1

Low sound 42 dB

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y48G28B09LS42



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)