

# Eaton Y48G28T09TRLS42

Catalog Number: Y48G28T09TRLS42

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 95, 60 Hz, three-phase, 480 V, 208Y/120 V, 2 at -5% FCBN, 115 °C rise, 9 KVA, indoor-outdoor, 70A

## General specifications



Photo is representative

### Product Name

Eaton General purpose encapsulated transformer

### Catalog Number

Y48G28T09TRLS42

### UPC

786680108549

### Product Length/Depth

10.52 in

### Product Height

17.38 in

### Product Width

20 in

### Product Weight

274 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

Low sound design equivalent to 42 dB, Certified Test Report of Standard Production Test (on CMI style)

## Physical Attributes

### Coil material

Aluminum

### Design

EPT

### Enclosure

NEMA 3R

### Frame

95

### Tap size

2 at -5% FCBN

### Type

General-purpose encapsulated transformer

### Wiring connection

70A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Three-phase

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Temperature rise

115 °C rise

### Volt ampere rating

9 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Y48G28T09TRLS42](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)