

Eaton Y48G31T45CUS6

Catalog Number: Y48G31T45CUS6

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 244, 60 Hz, three-phase, 480 V, 220Y/127 V, 2 at -5% FCBN, 115 °C rise, 45 KVA, indoor-outdoor, 66C



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48G31T45CUS6
	UPC
	786680089831
Product Length/Depth	Product Height
14.66 in	28.15 in
Product Width	Product Weight
26.58 in	0.001 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Grade 316 stainless steel enclosure

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

244

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

66C

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

220Y/127 V

Temperature rise

115 °C rise

Volt ampere rating

45 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y48G31T45CUS6](#)