

Eaton Y48G37T09X

Catalog Number: Y48G37T09X

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 95, 50-60 Hz, three-phase, 480 V, 380Y/220 V, 2 at -5% FCBN, 115 °C rise, 9 KVA, indoor-outdoor, 70A

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48G37T09X
	UPC
	786680013836

Product Length/Depth	Product Height
10.52 in	17.38 in

Product Width	Product Weight
20 in	278 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

95

Tap size

2 at -5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

70A

Performance Ratings

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

380Y/220 V

Temperature rise

115 °C rise

Volt ampere rating

9 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y48G37T09X](#)