

Eaton Y48M28B45CUESLS45

Catalog Number: Y48M28B45CUESLS45

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 245, 60 Hz, low sound 45 dB, three-phase, 480 V, 208Y/120 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 80 °C rise, 45 KVA, indoor-outdoor, 500A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48M28B45CUESLS45
	UPC
	786680099618
Product Length/Depth	Product Height
15.68 in	32.06 in
Product Width	Product Weight
30.29 in	1498 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Low sound equal to 45 dB

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

245

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

500A

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

80 °C rise

Volt ampere rating

45 kVA

Miscellaneous

Modification 1

Low sound 45 dB

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y48M28B45CUESLS45



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)