

Eaton Y48M28E15TR

Catalog Number: Y48M28E15TR

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 95, 60 Hz, three-phase, 480 V, 208Y/120 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 563A

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48M28E15TR
	UPC
	786680108600

Product Length/Depth	Product Height
10.52 in	17.38 in

Product Width	Product Weight
20 in	0.001 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

[Catalog Notes](#)

Certified Test Report of Standard Production Test (on CMI style)

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

95

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

563A

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y48M28E15TR



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)