

Eaton Y48M37T45CU

Catalog Number: Y48M37T45CU

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 244, 60 Hz, three-phase, 480 V, 380Y/220 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 45 KVA, indoor-outdoor, 84A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y48M37T45CU
	UPC
	786680108730
Product Length/Depth	Product Height
14.66 in	28.15 in
Product Width	Product Weight
26.58 in	809 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

244

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

84A

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

380Y/220 V

Temperature rise

115 °C rise

Volt ampere rating

45 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y48M37T45CU



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia