

Eaton Y57D28T75CU

Catalog Number: Y57D28T75CU

Eaton General purpose encapsulated transformer, EPT, copper, NEMA 3R, 245, 60 Hz, three-phase, 575 V, 208Y/120 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 115 °C rise, 75 KVA, indoor-outdoor, 65U



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y57D28T75CU
	UPC
	786685268149
Product Length/Depth	Product Height
15.68 in	32.06 in
Product Width	Product Weight
30.29 in	1539.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

EPT

Enclosure

NEMA 3R

Frame

245

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

65U

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

575 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Volt ampere rating

75 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y57D28T75CU



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia