

Eaton Y57D47T15

Catalog Number: Y57D47T15

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 95, 60 Hz, three-phase, 575 V, 480Y/277 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 72Z

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y57D47T15
	UPC
	786680099458

Product Length/Depth	Product Height
10.52 in	17.38 in

Product Width	Product Weight
20 in	268 lb

Warranty	Certifications
-----------------	-----------------------

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

95

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

72Z

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

575 V

Secondary Voltage

480Y/277 V

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y57D47T15](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)