

Eaton Y60M24T30N

Catalog Number: Y60M24T30N

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 243, 60 Hz, three-phase, 600 V, 240 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor, 85B



Photo is representative

General specifications

| | |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|
| Product Name | Catalog Number |
| Eaton General purpose encapsulated transformer | Y60M24T30N |
| | UPC |
| | 786680326417 |
| Product Length/Depth | Product Height |
| 10.52 in | 17.38 in |
| Product Width | Product Weight |
| 20 in | 422 lb |
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | Catalog Notes |
| | Model N |

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

243

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

85B

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

600 V

Secondary Voltage

240 V

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Y60M24T30N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)