

Eaton Y72M34T25X

Catalog Number: Y72M34T25X

Eaton General purpose encapsulated transformer, EPT, aluminum, NEMA 3R, 243, 50-60 Hz, three-phase, 200 V, 400Y/231 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 115 °C rise, 25 KVA, indoor-outdoor, 48C

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	Y72M34T25X
	UPC
	786680099496
Product Length/Depth	Product Height
10.52 in	17.38 in
Product Width	Product Weight
20 in	511 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EPT

Enclosure

NEMA 3R

Frame

243

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

48C

Performance Ratings

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

200 V

Secondary Voltage

400Y/231 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - Y72M34T25X



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia