

Eaton Z12N29S02

Catalog Number: Z12N29S02

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups a b c and d hazardous location transformer, EPZ, aluminum, 68H, 60 Hz, three-phase, 120 V, 208 V, None, 115 °C rise, 2 KVA, indoor-outdoor, 519X



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z12N29S02
	UPC
	786680115707

Product Length/Depth	Product Height
6.53 in	14.56 in

Product Width	Product Weight
11.21 in	53 lb

Warranty	Certifications
----------	----------------

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups A B C & D Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

120 V

Secondary Voltage

208 V

Temperature rise

115 °C rise

Design

EPZ

Frame

68H

Tap size

None

Volt ampere rating

2 kVA

Weathershield

Indoor-Outdoor

Wiring connection

519X

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z12N29S02](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)