

Eaton Z38G52T30CU

Catalog Number: Z38G52T30CU

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPTZ, copper, NEMA 3R, 243, 60 Hz, three-phase, 380 V, 460 V, 2 at - 2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor, 543G



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z38G52T30CU
	UPC
	786680077920

Product Length/Depth	Product Height
10.52 in	17.38 in

Product Width	Product Weight
20 in	656 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

380 V

Secondary Voltage

460 V

Temperature rise

115 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

243

Tap size

2 at -2.5% FCBN

Volt ampere rating

30 kVA

Weathershield

Indoor-Outdoor

Wiring connection

543G

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z38G52T30CU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)