

Eaton Z44D14B15CU

Catalog Number: Z44D14B15CU

Class 1 Div. 2 Groups A, B, C, and D Hazard Location Transformer, EPZ, Single-phase, Prim. voltage: 440V, Taps: 2 at +2.5% FCAN, 2 at -2.5% FCBN, Sec. voltage: 110/220V, 80°C, 15 kVA, Cu windings, FR180H, 16C, Indoor-Outdoor, 60 Hz, NEMA 3R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z44D14B15CU
	UPC 786680108808
Product Length/Depth	Product Height
10.53 in	19.68 in
Product Width	Product Weight
19.63 in	311 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups A, B, C, & D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

440 V

Secondary Voltage

110/220 V

Temperature rise

80 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

180H

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Volt ampere rating

15 kVA

Weathershield

Indoor-Outdoor

Wiring connection

16C

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z44D14B15CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)