

Eaton Z44G14S10XCU

Catalog Number: Z44G14S10XCU

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPZ, copper, NEMA 3R, 180H, 50-60 Hz, single-phase, 440 V, 110/220 V, NONE, 115 °C rise, 10 KVA, indoor-outdoor, 2H



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z44G14S10XCU
	UPC
	786685355122

Product Length/Depth	Product Height
10.53 in	19.68 in

Product Width	Product Weight
19.63 in	275 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Single-phase

Primary voltage

440 V

Secondary Voltage

110/220 V

Temperature rise

115 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

180H

Tap size

None

Volt ampere rating

10 kVA

Weathershield

Indoor-Outdoor

Wiring connection

2H

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z44G14S10XCU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)