

Eaton Z48D28B15CU

Catalog Number: Z48D28B15CU

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPTZ, copper, NEMA 3R, 243 H, 60 Hz, three-phase, 480 V, 208Y/120 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 80 °C rise



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48D28B15CU
	UPC
	786685355030

Product Length/Depth	Product Height
12.76 in	26.58 in

Product Width	Product Weight
25.15 in	624 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

80 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

243H

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Volt ampere rating

15 kVA

Weathershield

Indoor-Outdoor

Wiring connection

65H

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48D28B15CU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)