

Eaton Z48D29T09CUS6

Catalog Number: Z48D29T09CUS6

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPTZ, copper, NEMA 3R, 103H, 60 Hz, three-phase, 480 V, 208 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 115 °C rise



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48D29T09CUS6
	UPC
	786680099694
Product Length/Depth	Product Height
10 in	15.94 in
Product Width	Product Weight
21.37 in	234 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Grade 316 stainless steel enclosure

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208 V

Temperature rise

115 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

103H

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Volt ampere rating

9 kVA

Weathershield

Indoor-Outdoor

Wiring connection

232A

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48D29T09CUS6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)