

Eaton Z48G22T06X

Catalog Number: Z48G22T06X

Class 1 Div. 2 Groups A, B, C, and D Hazardous Location Transformer, EPTZ, Three-phase, Primary voltage: 480V, Taps: 2 at -5% FCBN, Secondary voltage: 240/120V, 115°C, 6 kVA, Aluminum windings, FR95H, 52A, Indoor-Outdoor, 50/60 Hz, NEMA 3R

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48G22T06X
	UPC 786680108815
Product Length/Depth	Product Height
10.52 in	17.78 in
Product Width	Product Weight
25.18 in	282 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups A, B, C, & D, Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

240 V, 120 V

Temperature rise

115 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

95H

Tap size

2 at -5% FCBN

Volt ampere rating

6 kVA

Weathershield

Indoor-Outdoor

Wiring connection

52A

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48G22T06X](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)