

Eaton Z48G22T09A

Catalog Number: Z48G22T09A

Class 1 Division 2 Groups C and D, Hazardous Location Transformer, EPTZ, Three-phase, PV: 480V, Taps: 2 at -5% FCBN, SV: 240 delta/120 midtap, 150°C, 9 kVA , Al windings, Frame: 243H, Indoor-Outdoor



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48G22T09A
	UPC
	786680009419
Product Length/Depth	Product Height
12.76 in	26.58 in
Product Width	Product Weight
25.15 in	605 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Catalog Notes
	Model A

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

240 V, 120 V

Temperature rise

150 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

243H

Tap size

2 at -5% FCBN

Volt ampere rating

9 kVA

Weathershield

Indoor-Outdoor

Wiring connection

62AA

Resources

Brochures

[Class 1, Division 2 Transformers](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48G22T09A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)