

# Eaton Z48G22T15A

Catalog Number: Z48G22T15A

Class 1 Division 2 Groups C and D, Hazardous Location Transformer, EPTZ, 3PH, PV: 480V, Taps: 2 at -5% FCBN, SV: 240 delta/120 midtap, 115°C, 15 kVA, Aluminium windings, Frame: 243H, Indoor-Outdoor



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48G22T15A
	UPC
	786680009426

Product Length/Depth	Product Height
12.76 in	26.58 in

Product Width	Product Weight
25.15 in	572 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Model A

[Catalog Notes](#)

Model A

## defaultTaxonomyAttributeLabel

### Type

Class 1 Division 2 Groups C and D, Hazardous Location  
Transformer

### Coil material

Aluminum

### Frequency rating

60 Hz

### Phase

Three-phase

### Primary voltage

480 V

### Secondary Voltage

240 V, 120 V

### Temperature rise

115 °C rise

### Design

EPTZ

### Enclosure

NEMA 3R

### Frame

243H

### Tap size

2 at -5% FCBN

### Volt ampere rating

15 kVA

### Weathershield

Indoor-Outdoor

### Wiring connection

52A

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Z48G22T15A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)