

Eaton Z48G22T30A

Catalog Number: Z48G22T30A

Class 1 Division 2 Groups C and D, Hazardous Location Transformer, EPTZ, 3PH, PV: 480V, Taps: 2 at -5% FCBN, SV: 240 delta/120 midtap, 115°C, 30 kVA, Al windings, Frame: 243H, Indoor-Outdoor



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48G22T30A
	UPC
	786680009433

Product Length/Depth	Product Height
12.76 in	25.5 in

Product Width	Product Weight
21.81 in	527 lb

Warranty	Compliances
-----------------	--------------------

Eaton Selling Policy 25-000, one (1) year Class I, Div. 2, Groups A, B, C, D from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications
UL Listed

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

240 V, 120 V

Temperature rise

115 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

243H

Tap size

2 at -5% FCBN

Volt ampere rating

30 kVA

Weathershield

Indoor-Outdoor

Wiring connection

62AA

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48G22T30A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)