

# Eaton Z48G28T09CUSS

Catalog Number: Z48G28T09CUSS

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPTZ, copper, NEMA 3R, 103H, 60 Hz, three-phase, 480 V, 208Y/120 V, 2 at -5% FCBN, 115 °C rise, 9 KVA, indoor-outdoor, 70A



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Hazardous location encapsulated transformer	Z48G28T09CUSS
	<b>UPC</b>
	786680069758
<b>Product Length/Depth</b>	<b>Product Height</b>
10 in	15.94 in
<b>Product Width</b>	<b>Product Weight</b>
21.37 in	235 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Catalog Notes</b>
	Grade 304 stainless steel enclosure

## defaultTaxonomyAttributeLabel

### Type

Class 1 Division 2 Groups C and D, Hazardous Location  
Transformer

### Coil material

Copper

### Frequency rating

60 Hz

### Phase

Three-phase

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Temperature rise

115 °C rise

### Design

EPTZ

### Enclosure

NEMA 3R

### Frame

103H

### Tap size

2 at -5% FCBN

### Volt ampere rating

9 kVA

### Weathershield

Indoor-Outdoor

### Wiring connection

70A

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Z48G28T09CUSS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)