

# Eaton Z48G28T15A

Catalog Number: Z48G28T15A

Eaton Hazardous location encapsulated transformer, Class 1 Division 2 Groups A, B, C, D Hazardous Location Transformer, Three-phase, PV: 480V, Taps: 2 at -5% FCBN, SV: 208Y/120V, 115°C, 15 kVA, Al windings, Indoor-Outdoor



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Hazardous location encapsulated transformer	Z48G28T15A
	<b>UPC</b>
	786680006265
<b>Product Length/Depth</b>	<b>Product Height</b>
10.52 in	17.78 in
<b>Product Width</b>	<b>Product Weight</b>
25.18 in	301 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year Not Applicable from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	UL Listed
	<b>Catalog Notes</b>
	Model A

## defaultTaxonomyAttributeLabel

### Type

Class 1 Division 2 Groups C and D, Hazardous Location  
Transformer

### Coil material

Aluminum

### Frequency rating

50/60 Hz

### Phase

Three-phase

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Temperature rise

115 °C rise

### Design

EPTZ

### Enclosure

NEMA 3R

### Frame

95H

### Tap size

2 at -5% FCBN

### Volt ampere rating

15 kVA

### Weathershield

Indoor-Outdoor

### Wiring connection

70A

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Z48G28T15A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)