

Eaton Z48G28T30CUS6

Catalog Number: Z48G28T30CUS6

30 KVA Class 1 Division 2 Groups A, B, C, D Hazardous Location Transformer, 3PH, 480V DELTA-208Y/120V, 115C Rise, Copper windings, 316SS NEMA 3R Enclosure



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48G28T30CUS6
	UPC
	786680099717
Product Length/Depth	Product Height
12.76 in	26.58 in
Product Width	Product Weight
25.15 in	611 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Not Applicable from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	Grade 316 stainless steel enclosure

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

243H

Tap size

2 at -5% FCBN

Volt ampere rating

30 kVA

Weathershield

Indoor-Outdoor

Wiring connection

66A

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48G28T30CUS6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)