

Eaton Z48G28T75XCU

Catalog Number: Z48G28T75XCU

Eaton Class 1 Division 2 Groups C and D, Hazardous Location Transformer, EPTZ, Three-phase, PV: 480V, Taps: 2 at -5% FCBN, SV: 208Y/120V, 115°C, 75 kVA, Cu windings, Indoor-Outdoor, Frame: 245H



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48G28T75XCU
	UPC
	786680069765

Product Length/Depth	Product Height
15.68 in	31.98 in

Product Width	Product Weight
46.23 in	1680 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

245H

Tap size

2 at -5% FCBN

Volt ampere rating

75 kVA

Weathershield

Indoor-Outdoor

Wiring connection

66A

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48G28T75XCU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)