

Eaton Z48G47T45CUSS

Catalog Number: Z48G47T45CUSS

Class 1 Division 2 Groups C and D, Hazardous Location Transformer, EPTZ, 3PH, PV: 480V, Taps: 2 at -5% FCBN, SV: 480Y/277V, 115°C, 45 kVA, Cu windings, Frame: 244H, Indoor-Outdoor



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48G47T45CUSS
	UPC
	786680057137
Product Length/Depth	Product Height
12.76 in	26.58 in
Product Width	Product Weight
25.15 in	1650 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Grade 304 stainless steel enclosure

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Temperature rise

115 °C rise

Design

EPTZ

Enclosure

NEMA 3R

Frame

244H

Tap size

2 at -5% FCBN

Volt ampere rating

45 kVA

Weathershield

Indoor-Outdoor

Wiring connection

66A

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48G47T45CUSS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)